

- 9 MAX COMPONENT HEIGHT DOES NOT INCLUDE MATED CABLES.
  - 8 IT IS RECOMMENDED THAT ADJACENT PCB'S AND SURFACES BE KEPT .242 [6.15] FROM THE SECONDARY SIDE SURFACE.
  - 7 IT IS RECOMMENDED THAT ADJACENT PCB'S AND SURFACES BE KEPT .750 [19.05] FROM THE PRIMARY SIDE SURFACE.
  - 6 RECOMMENDED PANEL THICKNESS RANGE IS FROM .032 [0.81] TO .100 [2.54].
  - 5 4-40 MAX TORQUE 3.6 IN LBS.
  - 4 DAUGHTER CARD COMPONENTS SHOULD NOT EXTEND ABOVE THIS KEEPOUT LINE.
  - 3 HOLES AND KEEPOUTS SIZED FOR M3 STANDOFF (4.5 HEX) OR 4-40 STANDOFF (0.1875 HEX). MAX SCREW HEAD OR STANDOFF DIAMETER OF 0.236 [6 MM].
  - 2 LATCH ON MATING PLUG REQUIRES CLEARANCE UP TO THIS HEIGHT.
1. REFER TO PRODUCT MANUAL ON NI.COM FOR MORE DETAILS.  
 NOTES: UNLESS OTHERWISE SPECIFIED.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND [MILLIMETERS].

DO NOT SCALE DRAWING  
 THIRD ANGLE PROJECTION


**NATIONAL INSTRUMENTS®** AUSTIN, TEXAS

TITLE  
 CUSTOMER DRAWING,  
 sbRIO-9633\_36

SIZE CODE IDENT NO | MM/DD/YYYY  
 D | 7U296 | 03/13/2012

SCALE: 2/1 SHEET 1 OF 2  
 CU.SBRIO-9633.36

9 MAX COMPONENT HEIGHT = 0.375 [9.53]



MAX COMPONENT HEIGHT = 0.242 [6.15]

