



PN: 2444
 AVAILABLE RANGE: 0-80 THRU 0-300 LBS.
 BRIDGE RESISTANCE: 350 OHM (FOIL)
 EXCITATION: 5 VDC
 OUTPUT: 2 mV/ V NOMINAL

UNAMPLIFIED

COLOR	DESIGNATION
RED	(+) EXCITATION
BLACK	(-) EXCITATION
GREEN	(-) OUTPUT
WHITE	(+) OUTPUT

UNLESS OTHERWISE SPECIFIED:
 ALL FILLETS & CORNERS .005 R MAX
 ALL DIMENSIONS IN INCHES
 INTERPRET PER ANSI Y14.5M-1982 &
 SENSOTEC STD 080-0073-00
 DEBURR & BREAK SHARP CORNERS

A	REDRAWN PER ECN #14	TEM 5-12-98	RAF 05/12/98
REV	DESCRIPTION	REVISED BY	APPROVED BY
DRW: 8-2-82	RLR	CHK: 7-27-87	RLF MFG: ENG:
SENSOTEC INC. 2080 ARLINGATE LANE, COLUMBUS, OHIO 43228 © SENSOTEC, INC. ALL RIGHTS RESERVED			
MODEL 13 LOAD CELL P/N 2444		XXX XXX	
		DOCUMENT NUMBER	
		000-1452-00	
045-	SCALE: NONE .X ±.1 .XX ±.01 .XXX ±.005 ±1/2"	63	SHEET 1 OF 1